

## **SIL SG102-07    Service Information Letter SG102 AHRS**

---

Date:                    March 6, 2014  
Regarding:            SG102 AHRS MOD 2 Release  
SIL Revision:         B (See change bars)

### **Reason**

This Service Information Letter announces the availability of an improved SG102 (MOD 2).

### **Applicability**

Future SG102 shipments.

### **Compliance**

Not required. Informational only.

### **Description**

Features:

- Provides selectable high speed ARINC 429.
- Initialization time reduced to 1 minute nominal.

SG102 MOD 2 units, except for the specifications, are interchangeable with prior SG102 units.

Note: The mounting orientation for the SG102 MOD 2 has been inverted on the mounting plate compared to prior MOD levels. See SG102 Installation Manual Revision G2 (or later).

Version 2.60 of the SG102 Installation/Calibration Utility Software is now available which enables selection of high or low speed ARINC 429.

### **Warranty Reimbursement**

N/A

## **Manpower**

N/A

## **Approval**

This modification does not affect the original approval.

Contact Sandel for details if needed.

## **Identification**

TSO label indicates MOD 2

## **Testing**

None required.

## **Related Documentation**

82011-IM Rev. G2 (or later)

Installation Manual

82011-PGERR Rev. D5

Pilots Guide Errata

82011-ICUG Rev. E

Installation/Calibration Utility User Guide

**END**